



Operating Instructions (continued)

DEVICE FLOW SETTINGS AVAILABLE FOR EACH FUSE SETTING

Setting	AVAILABLE WITH 10 AMP		AVAILABLE WITH 15 AMP	
	Continuous	Pulse	Continuous	Pulse
0.5	Yes	Not Available	Yes	Not Available
1.0	Yes	Yes	Yes	Yes
1.5	Yes	Yes	Yes	Yes
2.0	Yes	Yes	Yes	Yes
2.5	NO	Yes	Yes	Yes
3.0	NO	Yes	Yes	Yes
3.5	-	Yes	-	Yes
4.0	-	Yes	-	Yes
4.5	-	Yes	-	Yes
5.0	-	Yes	-	Yes
5.5	-	Yes	-	Yes
6.0	-	Yes	-	Yes

NOTE: Actual performance may vary depending upon usage conditions and the motor vehicle.

NOTE: When operating in the 10 AMP switch position, with device flow settings greater than 2.0 LPM continuous flow, the device will automatically switch to the 2.0 LPM continuous flow setting when the DC Power Supply is connected to conserve DC power and improve duration-of-use.